

# FPM-300

POWER METER



The FPM-300 Power Meter is part of EXFO's new line of handheld units, which includes the FLS-300 Light Source and the FOT-300 Optical Loss Test Set.

## KEY FEATURES

Highly accurate unit offering 10 calibrated wavelengths and reference values

Power autonomy of 300 hours

Three-year warranty and recommended calibration interval, for dramatically reduced cost of ownership

Ergonomic, eye-catching handheld package

SPEC SHEET



## AUTO-WAVELENGTH RECOGNITION

The FLS-300 or FOT-300 units can transmit with a wavelength-identification digital encrypted protocol, enabling the FPM-300 Power Meter to automatically use the proper calibration parameters. This feature reduces the need for communication between the two technicians and decreases the potential for error.

## DISTANT REFERENCING

Signal encrypting can also give the receiving end information on the power to be used as reference, helping ensure efficient referencing, even when the two units are far apart.

## FTTx READY

EXFO's FPM-300 allows for the testing of passive optical networks (PONs) at 1310 nm, 1490 nm and 1550 nm, the three wavelengths recommended by the ITU-T (G.983.3) for PONs.

### SPECIFICATIONS <sup>a</sup>

Model <sup>b</sup>	FPM-302	FPM-302X
Power meter port	Ge	GeX
Power range (dBm) <sup>c</sup>	10 to –60	26 to –50
Range displayed (dBm)	Down to –65	Down to –50
Number of calibrated wavelengths <sup>d</sup>	10	10
Power uncertainty <sup>e</sup>	±5 % ± 0.1 nW	±5 % ± 10 nW
Resolution (dB)	0.01 <sup>f</sup>	0.01 <sup>g</sup>
Automatic offset nulling <sup>h</sup>	Yes	Yes
Warm-up period (min) <sup>i</sup> (s)	0	0
Display units	dB, dBm, W	dB, dBm, W
Tone detection	270 Hz, 1 kHz and 2 kHz	270 Hz, 1 kHz and 2 kHz
Automatic wavelength recognition <sup>j</sup>	Yes	Yes
Screen refresh rate (Hz)	3	3
Tone detection (Hz)	270, 1 k, 2 k	270, 1 k, 2 k
Battery life (hours) (typical)	> 300	> 300
Warranty and recommended recalibration interval (years)	3	3

### GENERAL SPECIFICATIONS

Size (H x W x D)	185 mm x 100 mm x 55 mm (7 ¼ in x 4 in x 2 ½ in)
Weight	0.4 kg (0.9 lb)
Temperature operating storage	–10 °C to 50 °C (14 °F to 122 °F) –40 °C to 70 °C (–40 °F to 158 °F)
Relative humidity	0 % to 95 % noncondensing

### STANDARD ACCESSORIES

User guide, certificate of calibration, instrument stickers in six languages, AC adapter, three AA batteries, wrist strap and carrying case.

#### NOTES

- Guaranteed unless otherwise specified.
- All specifications valid at 1550 nm and 23 °C ± 1 °C, with an FC connector.
- In CW mode; sensitivity defined as 6 x rms noise level.
- Wavelengths: 830 nm, 850 nm, 980 nm, 1300 nm, 1310 nm, 1450 nm, 1490 nm, 1550 nm, 1590 nm and 1625 nm.
- Traceable to NIST; FPM-302X: up to 20 dBm.
- From 10 dBm to –50 dBm.
- From 26 dBm to –35 dBm.
- Power of > –40 dBm for FPM-302, and of > –25 dBm for FPM-302X.
- For ± 0.05 dB and temperatures of > 18 °C.
- At 850 nm, 1300 nm, 1310 nm, 1490 nm, 1550 nm and 1625 nm; power of > –50 dBm for FPM-302, and of > –40 dBm (typical) for FPM-302X.



## ORDERING INFORMATION

## FPM-30X-XX

## Model

FPM-302 = Ge detector  
 FPM-302X = High-power Ge detector

## Connector adapter

FOA-12 = Biconic  
 FOA-14 = D4, D4/PC  
 FOA-16 = SMA/905, SMA-906  
 FOA-22 = FC (PC/SPC/UPC/APC), NEC-D3  
 FOA-28 = DIN 47256 (LSA): DIN 47256 (PC/APC)  
 FOA-32 = ST (PC/SPC/UPC)  
 FOA-54 = SC (PC/SPC/UPC/APC)  
 FOA-76 = FSMA HMS-10/AG, HFS-10/AG  
 FOA-78 = Radiall EC  
 FOA-84 = Diamond HMS-10, HFS-13  
 FOA-96B = E-2000  
 FOA-98 = LC  
 FOA-99 = MU

Example: FPM-302X-FOA-22

EXFO Headquarters > Tel.: +1 418 683-0211 | Toll-free: +1 800 663-3936 (USA and Canada) | Fax: +1 418 683-2170 | info@EXFO.com | [www.EXFO.com](http://www.EXFO.com)

EXFO serves over 2000 customers in more than 100 countries. To find your local office contact details, please go to [www.EXFO.com/contact](http://www.EXFO.com/contact).

EXFO is certified ISO 9001 and attests to the quality of these products. EXFO has made every effort to ensure that the information contained in this specification sheet is accurate. However, we accept no responsibility for any errors or omissions, and we reserve the right to modify design, characteristics and products at any time without obligation. Units of measurement in this document conform to SI standards and practices. In addition, all of EXFO's manufactured products are compliant with the European Union's WEEE directive. For more information, please visit [www.EXFO.com/recycle](http://www.EXFO.com/recycle). Contact EXFO for prices and availability or to obtain the phone number of your local EXFO distributor.

For the most recent version of this spec sheet, please go to the EXFO website at [www.EXFO.com/specs](http://www.EXFO.com/specs).

In case of discrepancy, the Web version takes precedence over any printed literature.

Keep this document for future reference.