



**Twist-Lock Pump:**

- Lockable for travel – twist pump clockwise to engage lock, counterclockwise to disengage
- One touch operation frees operator’s hands for use
- Spill and leak resistant design reduces fumes and waste
- Recommended for one-handed dispensing of liquids, solvents, and chemicals
- Durable, light-weight construction
- Dispenses approximately 0.7cc of liquid with each pump
- Compatible with any 24-410 threaded neck container
- Made in Mexico

<b>Pump Material</b>	Polypropylene
<b>Spring Material</b>	Stainless-Steel
<b>Locks for Travel</b>	Yes
<b>Neck Size/Thread</b>	24/410
<b>Lid-Type</b>	Hinge lid

**Pump Care:**

Some types of fluids may leave a residue in the mechanism of the dispenser. Over time, this can reduce the performance of the pump. Occasional cleaning is recommended to maintain your unit to original efficiency.

Clean by flushing the mechanism thoroughly with warm soapy water. Flush the mechanism again with clean water to remove any soap residue. Do not boil or steam the dispenser. For long periods of inactivity, pumps should be flushed free of liquid and stored inverted in a dry place.

**Limited Warranty, Warranty Exclusions, Limit of Liability and RMA Request Instructions:**

Before using, users shall determine the suitability of the product for their intended use, and users assume all risk and liability whatsoever in connection therewith. See the Menda Terms and Conditions - [Mendapump.com/TermsAndConditions.aspx](http://Mendapump.com/TermsAndConditions.aspx)

Specifications and procedures subject to change without notice. *Unless otherwise noted, tolerance is ±10%.*

**TWIST-LOCK, PUMP ONLY**

[FiberOpticBank.com](http://FiberOpticBank.com)

**MENDA**

3651 WALNUT AVE., CHINO, CA 91710  
 PHONE: (909) 627-2453  
 WEBSITE: [MendaPump.com](http://MendaPump.com)

**DRAWING NUMBER**  
35200

**DATE:**  
April  
2016